



Accura[®] SL Y-C 9300

Selectively colorable stereolithography material

Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	45	6525
Tensile Modulus (MPa/KSI)	ASTM D 638	1315	191
Elongation at Break (%)	ASTM D 638	7	7
Glass Transition (Tg)	DMA, E"	52 °C	126 °F
Hardness, Shore D	ASTM D 2240	75	75
Density		1.18 g/cm ³	1.18 g/cm ³

Features

- Clear parts with selectively-colored areas
- Capable of meeting the standards of USP Class VI
- Parts can be sterilized
- Ideal to show differences in design iterations
- Ideal for medical applications
- Ideal for improved visualization within parts

Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	1150 cps
Penetration Depth (Dp)		9.4 mils
Critical Exposure (Ec)		8.4 mJ/cm ²
Color		Clear
Density	@ 25 °C (77 °F)	1.12 g/cm ³
Critical energy for coloration (Ecc)	@ 30 °C (86 °F)	>320 mJ/cm ²



SOLIDLINE
INNOVATING YOUR BUSINESS



www.solidline.de



3d-druck@solidline.de



0800 76 54 396

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use. © 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, and Accura are registered trademarks of 3D Systems, Inc.